















Features

- · 4"x2" miniature size
- Universal AC input / Full range
- · Built-in active PFC function
- · EMI Class B for both Class I (with FG) and Class II (without FG) configuration
- · Medical safety approved (2 x MOPP between primary to secondary)
- Suitable for BF application with appropriate system consideration
- Low leakage current <190µA
- No load power consumption<0.5W
- · High efficiency up to 94%
- · Protections: Short circuit / Overload / Over voltage / Over temperature
- Cooling by free air convection for 140W and 200W with 10CFM forced air
- Built-in 12V/0.5A fan supply
- · LED indicator for power on
- 3 years warranty


Applications

- Oral irrigator
- Hemodialysis machine
- · Medical monitors
- Sleep apnea devices
- · Pumps machine
- · Electric bed

Description

RPS-200 is a 200W highly reliable green PCB type medical power supply with a high power density (21.9W/in³) on the 4" by 2" footprint. It accepts 80~264VAC input and offers various output voltages between 12V and 48V. The working efficiency is up to 94% and the extremely low no load power consumption is down below 0.5W. RPS-200 is able to be used for both Class I (with FG) and Class II (no FG) system design. The extremely low leakage current is less than 190µA. In addition, it conforms to the international medical regulations (2*MOPP) and EMC EN55011, perfectly fitting all kinds of BF rated "patient contact" medical system equipment.

Model Encoding






200W Single Output Medical Type

SPECIFICATION


MODEL		RPS-200-12	RPS-200-15	RPS-200-24	RPS-200-27	RPS-200-48		
	DC VOLTAGE		12V	15V	24V	27V	48V	
		10CFM	16.7A	13.4A	8.4A	7.5A	4.2A	
	CURRENT	Convection	11.7A	9.4A	5.9A	5.3A	3A	
	RATED	10CFM	200.4W	201W	201.6W	202.5W	201.6W	
	POWER	Convection	140.4W	141W	141.6W	143.1W	144W	
	RIPPLE & NOISE (max.) Note.2			100mVp-p	150mVp-p	150mVp-p	200mVp-p	
OUTPUT	VOLTAGE ADJ. RANGE		11.4~12.6V	14.3~15.8V	22.8~25.2V	25.6 ~ 28.4V	45.6 ~50.4V	
	VOLTAGE TOLERANCE Note.3		-	±2.0%	±1.0%	±1.0%	±1.0%	
	LINE REGULATION		±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	
	LOAD REGULATION		±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	
	SETUP, RISE TIME					1.070	1.070	
	HOLD UP TIME (Typ.)		700ms, 30ms/230VAC 700ms, 30ms/115VAC at full load 12ms/230VAC 12ms/115VAC at full load					
	, , , ,							
	VOLTAGE RANGE Note.4							
	FREQUENCY RANGE		47 ~ 63Hz					
	POWER FACTOR		PF>0.94/230VAC PF	T T	1	0.407	0.40/	
NPUT	EFFICIENCY (Typ.)		93%	93%	94%	94%	94%	
	AC CURRENT (Typ.)			30VAC				
	INRUSH CURRENT (Typ.)		COLD START 30A/115VAC 60A/230VAC					
	LEAKAGE CURRENT Note.5		Earth leakage current < 190μA/264VAC , Touch current < 100μA/264VAC					
	OVERLOAD		110 ~ 140% rated output power					
	OVERLOAD		Protection type : Hiccup mode, recovers automatically after fault condition is removed					
ROTECTION	OVER VOLTAGE		13.2 ~ 15.6V	16.5 ~ 19.5V	26.4 ~ 31.2V	29.7 ~ 35V	52.8 ~ 62.4V	
			Protection type : Shut down o/p voltage, re-power on to recover					
	OVER TEMPERATURE		Protection type : Shut down o/p voltage, re-power on to recover					
UNCTION	FAN SUPPLY		12V@0.5A for driving a fan ; tolerance +15% ~ -15%					
	WORKING TEMP.		-30 ~ +70°C (Refer to "Derating Curve")					
	WORKING HI	JMIDITY	20 ~ 90% RH non-condensing					
ENVIRONMENT	STORAGE TEI	MP., HUMIDITY	' -40 ~ +85°C, 10 ~ 95% RH					
	TEMP. COEFFICIENT		±0.03%/°C (0~50°C)					
	VIBRATION		10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes					
	SAFETY STANDARDS		ANSI/AAMI ES60601-1, TUV EN60601-1, IEC60601-1 approved					
	ISOLATION RESISTANCE							
SAFETY &	WITHSTAND VOLTAGE		I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.5KVAC					
EMC (Note 6)			I/P-O/P, I/P-FG:100M Ohms / 500VDC / 25°C / 70% RH					
11010 0,	EMC EMISSION	ON	Compliance to EN55011 (CISPR11) Class B, EN61000-3-2,-3					
	EMC IMMUNI		Compliance to EN61000-4-2,3,4,5,6,8,11, EN55024, EN60601-1-2, medical level, criteria A					
	MTBF		500.2Khrs min. MIL-HDBK-217F (25°C)					
OTHERS	DIMENSION		PCB:101.6*50.8*29mm (L*W*H); Enclosed type:103.4*62*40mm (L*W*H)					
UTILING			PCB:0.19Kg; 72pcs/14.7Kg/0.82CUFT; Enclosed type:0.3Kg; 60pcs/19Kg/1.12CUFT					
NOTE	All parame Ripple & r Tolerance Derating r Touch cur The powe mounting EMC dire	noise are mea includes set may be neede rent was mea r supply is con the unit on a ctives. For gui	respecially mentioned are measured at 230VAC input, rated load and 25 of ambient temperature. measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. In second under low input voltages. Please check the derating curve for more details. measured from primary input to DC output. so considered a component which will be installed into a final equipment. All the EMC tests are been executed by an a 360mm*360mm metal plate with 1mm of thickness. The final equipment must be re-confirmed that it still meets or guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies."					

200W Single Output Medical Type





200W Single Output Medical Type



DC Output Connector (CN2): JST B6P-VH or equivalent

Pin No.	Assignment	Mating Housing	Terminal	
1,2,3	+V	JST VHR	JST SVH-21T-P1.1	
4,5,6	-V	or equivalent	or equivalent	

FAN Connector(CN101): JST B2B-PH-K-S or equivalent

Pin No.	Assignment	Mating Housing	Terminal				
1	DC COM	JST PHR-2	JST SPH-002T-P0.5S				
2	+12V	or equivalent	or equivalent				

- **Note: 1. The FAN supply is designed to serve as the source of the additive external fan for the cooling of the power supply, enabling the full load delivery and assuring the best life span of the product. Please do not use this FAN supply to drive other devices.
 - 2.The PCB type(Blank type)model delivers EMI Class B for both conducted emission and radiated emission for the power supply, when configured into either Class I (with FG) or Class II (without FG) system.
 - 3.The Enclosed type(-C type) model is not suitable for the configuration within a Class II (without FG) system but is suggested to used within a Class I (with FG) system.

■ Installation Manual

Please refer to: http://www.meanwell.com/webnet/search/InstallationSearch.html